

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151330700](#)
Status: **Active**
Overview: [Pico-Clasp™ Wire-to-Board Connectors](#)
Description: [Pico-Clasp™-to-Pico-Clasp™ Off-the-Shelf \(OTS\) Cable Assembly, Single Row, 50.00mm Length, 7 Circuits, White](#)

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	15133
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Pico-Clasp™-to-Pico-Clasp™
Overview	Pico-Clasp™ Wire-to-Board Connectors
Product Literature Order No	987651-6143
Product Name	Pico-Clasp™ OTS
UPC	191128137904

Physical

Cable Length	50.00mm
Circuits (Loaded)	7
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.710/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.60mm
Wire Size AWG	28
Wire/Cable Type	UL 1571


Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2012341667-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -
ED/21/2016 (20 June
2016)
2,4-Di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[15133 Series](#)

Mates With

[501331](#) , [501568](#) PCB Header