



ENGLISH

Datasheet

RS Pro Insulated Pliers

Stock No: 125-3065



Product Details

RS Pro G10 Series Insulated combination pliers. Ideal for working up to 1000 V ac or 1500 V dc. Suitable for cutting soft and hard wire.

- Special tool steel
- Chrome finish
- DuoTech soft grip handles
- VDE Approved
- ISO 5746
- G10 Series

Specification

| | | |
|-----------------------------|--|----|
| Cutting Capacity Hard Wire | 1.8 | mm |
| Cutting Capacity Soft Wire | 1.8 | mm |
| Cutting Capacity | Maximum of 1.8 (Hard Wire) mm, Maximum of 1.8 (Soft Wire) mm | |
| Jaw Length | 35 | mm |
| Material Cutting Capability | Hard Wire, Soft Wire | |
| Material | Steel | |
| Maximum Capacity | 1.8 | mm |
| Overall Length | 160 | mm |
| VDE/1000V Approved | Yes | |