



ENGLISH

Datasheet

RS Pro Insulated Pliers

Stock No: 125-3066



Product Details

RS Pro G10 Series Insulated combination pliers. Ideal for working up to 1000 V ac or 1500 V dc. Suitable for cutting soft and hard wire.

- Special tool steel
- Chrome finish
- DuoTech soft grip handles
- VDE Approved
- ISO 5746
- G10 Series

Specification

Cutting Capacity Hard Wire	2	mm
Cutting Capacity Soft Wire	2	mm
Cutting Capacity	Maximum of 2 (Hard Wire) mm, Maximum of 2 (Soft Wire) mm	
Jaw Length	29	mm
Material Cutting Capability	Hard Wire, Soft Wire	
Material	Steel	
Maximum Capacity	2	mm
Overall Length	180	mm
VDE/1000V Approved	Yes	