



ENGLISH

Datasheet

RS Pro 6070 Digital Thermometer, 1 Input Probe

RS Stock No: 465-9218



Product Details

RS Pro digital thermometer comes with 1 input stainless steel probe, rubberised handle and 1 x AAA battery. It has maximum or minimum memory.

Features and Benefits

- Overall dimensions of 290 x 40 x 27 mm
- 4 mm dia., 130 mm long probe
- 1 input probe

**Specifications:**

Absolute Maximum Temperature Measurement	+200°C
Application	Multi-Purpose
Battery Type	AAA
Best Accuracy	+/- 1°C
Dimensions	290 x 40 x 27 mm
Height	27 mm
Length	290 mm
Minimum/Maximum Recordings	Yes
Number of Temperature Inputs	1
Resolution	0,1°C
Temperature Scale	Centigrade, Fahrenheit
Thermometer Type	Probe
Weight	60 g
Width	40 mm
Instrument Measurement Range	0 to +200°C