



ENGLISH

Datasheet

RS Pro Motor - Extruder

Stock No: 136-3550



Specifications:

Size:	42 x 42 x 68mm
Step angle (°):	18
Flange size:	42.3max
Ambient temperature:	-20~50°C
Insulation resistance:	100MΩmin, DC500V
Withstand voltage:	AC500V One minute
Radial clearance:	0.02max. (450g load)
Axial clearance:	0.08max. (450g load)
Radial maximum load: (from the flange surface 20mm)	28N
Axial maximum load:	10N