



# MASTER LEDspot ExpertColor MV

## MASTER LED ExpertColor 5.5-50W GU10 940 25D

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV and LEDspot Par lamps.

### Product data

General Information	
Cap-Base	GU10 [ GU10]
Nominal Lifetime (Nom)	40000 h
Switching Cycle	50000X
Technical Type	5.5-50W
Light Technical	
Color Code	940 [ CCT of 4000K]
Beam Angle (Nom)	25 °
Luminous Flux (Nom)	400 lm
Luminous Flux (Rated) (Nom)	400 lm
Luminous Intensity (Nom)	1050 cd
Color Designation	Cool White (CW)
Rated Beam Angle	25 °
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	72.73 lm/W

Color Consistency	<3
Color Rendering Index (Nom)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux In 90° Cone (Rated)	400 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	5.5 W
Lamp Current (Nom)	30 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	220-240 V

# MASTER LEDspot ExpertColor MV

## Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application

Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	6 kWh

## Product Data


Full product code	871869670765400
Order product name	MASTER LED ExpertColor 5.5-50W GU10 940 25D
EAN/UPC - Product	8718696707654
Order code	929001347202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001347202
Net Weight (Piece)	0.038 kg

## Dimensional drawing

Product	D	C
MASTER LED ExpertColor 5.5-50W GU10 940 25D	50 mm	54 mm

GU10 230V5.5W-50W360lm25D 4000K GU10 Dim

## Photometric data



MASTER LEDspot ExpertColor MV 50W GU10 940 25D

# MASTER LEDspot ExpertColor MV

