


Datasheet - PDM-SD-4CC-SD

Input expander / PDM



- For SD-Interface devices
- Passive distribution module for series-wiring
- Cage clamps
- For up to 4 safety switchgears
- Fuse protected device ports
- For installation in terminal boxes
- Protection class IP00

(Minor differences between the printed image and the original product may exist!)

Ordering details

Product type description	PDM-SD-4CC-SD
Article number	103012161
EAN code	
eCl@ss	

Approval

Approval



Global Properties

Product name	PDM
Standards	IEC 60947-1
Application	
Materials	
- Material of the housings	Plastic, Polyamide
Weight	120 g

Mechanical data

Design of electrical connection	Cage clamps
Cable section	

- Min. Cable section	0,25 mm ²
- Max. Cable section	1.5 mm ²
notice	All indications about the cable section are including the conductor ferrules.
restistance to shock	30 g / 11 ms
Resistance to vibration	10 ... 55 Hz, Amplitude 1 mm

Ambient conditions

Ambient temperature	
- Min. environmental temperature	-25 °C
- Max. environmental temperature	+65 °C
Storage and transport temperature	
- Min. Storage and transport temperature	-40 °C
- Max. Storage and transport temperature	+85 °C
Relative humidity	5 ... 95 %, non-condensing
Protection class	IP00
Protection rating	III
Insulation values to IEC 60664-1	
- Rated impulse withstand voltage U _{imp}	0,8 kV
- Rated insulation voltage U _i	32 VDC
- Overvoltage category	III
- Degree of pollution	2

Electrical data

Supply voltage U _B	24 VDC -15% / +10% (stabilised PELV)
Rated operating voltage U _e	24 VDC
Operating current I _e	
- Passive distribution module ()	10 A
- ()	1.5 A

LED switching conditions display

LED switching conditions display (Y/N)	Yes
Number of LED's	5 piece

ATEX

Explosion protection Zones for gases	None
Explosion protection Zones for dusts	None

Dimensions

Dimensions	
- Width	45 mm
- Height	105.4 mm
- Depth	67.7 mm

Documents

Operating instructions and Declaration of conformity (de) 782 kB, 21.06.2016

Code: mrl_pdm-sd-4cc-sd_de

Operating instructions and Declaration of conformity (fr) 775 kB, 21.07.2016

Code: mrl_pdm-sd-4cc-sd_fr

Operating instructions and Declaration of conformity (nl) 781 kB, 24.06.2016

Code: mrl_pdm-sd-4cc-sd_nl

Operating instructions and Declaration of conformity (pt) 766 kB, 21.07.2016

Code: mrl_pdm-sd-4cc-sd_pt

Operating instructions and Declaration of conformity (pl) 777 kB, 22.11.2016

Code: mrl_pdm-sd-4cc-sd_pl

Operating instructions and Declaration of conformity (en) 793 kB, 21.06.2016

Code: mrl_pdm-sd-4cc-sd_en

Operating instructions and Declaration of conformity (it) 795 kB, 24.06.2016

Code: mrl_pdm-sd-4cc-sd_it

Operating instructions and Declaration of conformity (es) 764 kB, 19.07.2016

Code: mrl_pdm-sd-4cc-sd_es

Images

K.A. Schmersal GmbH & Co. KG, Möddinghofe 30, D-42279 Wuppertal

The data and values have been checked thoroughly. Technical modifications and errors excepted.

Generiert am 05.10.2017 - 11:09:38h Kasbase 3.2.7.F.64I