

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1042380210](#)
Status: **Active**
Overview: [Lite-Trap and Mini Lite-Trap Connector System](#)
Description: Mini Lite-Trap SMT Wire-to-Board Connector, Push-Button Type, 2 Circuits

Documents:

[3D Model](#) [Packaging Specification PK-104238-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-104238-001-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Receptacles
 Series [104238](#)
 Application Wire-to-Board
 Overview [Lite-Trap and Mini Lite-Trap Connector System](#)
 Product Name Mini Lite-Trap
 UPC 889056065337

Physical

Circuits (Loaded) 2
 Circuits (maximum) 2
 Color - Resin Natural
 Durability (mating cycles max) 25
 Glow-Wire Compliant No
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Material - Resin Liquid Crystal Polymer
 Net Weight 0.175/g
 Number of Rows 1
 Orientation Right Angle
 PCB Retention None
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 3.00mm
 Plating min - Mating 0.800µm
 Polarized to PCB No
 Temperature Range - Operating -40°C to +130°C
 Termination Interface: Style Surface Mount


Electrical

Current - Maximum per Contact 3.0A
 Voltage - Maximum 160V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification PK-104238-001-001
 Product Specification PS-104238-001-001
 Sales Drawing SD-104238-003, SD-104238-004



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[104238 Series](#)