

## SKINDICHT® SM-M

SKINDICHT® SM-M, metric counter nuts for through-holes on thin-walled housings



Mechanical resistance



Good chemical resistance

### Application range

Used when a gland has to be countered, or in through-holes on thin-walled housings

### Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

### Technical Data

Classification:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-70°C to +100°C

### Note

Photographs are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® SM-M**

Article number	Article designation / size	Thickness (mm)	SW mm	Outer Ø (mm)
SKINDICHT® SM-M				
52103000	M 12 x 1,5	3	15	16.5
52103010	M 16 x 1,5	3	19	20.9
52103020	M 20 x 1,5	3.5	24	26.4
52103030	M 25 x 1,5	4	30	33
52103040	M 32 x 1,5	4	36	39.6
52103050	M 40 x 1,5	5	46	50.6
52103060	M 50 x 1,5	5	60	65
52103070	M 63 x 1,5	5	70	77
52103071	M 75 x 1,5	8	85	95
52103072	M 90 x 2	10	102	114
52103073	M 110 x 2	12	124	135

Last Update (04.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16