



D25334K

30mm L-Shape SDS-Plus Combination Hammer With Quick Change Chuck

Selling Proposition

- Category-leading high speed drilling performance
- Rotation stop mode for light chiselling in soft masonry, plaster, tiles and light concrete and impact-stop mode for rotary only drilling in wood and metal
- Perform & Protect: best-in-class vibration at 7.8m/s², minimising user fatigue
- Mechanical clutch reduces sudden high-torque reaction should the bit jam
- Compact, lightweight and ergonomic design for improved comfort and support during extended operating periods
- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 30mm

Standard Equipment

- Depth stop
- Multi-position side handle
- Quick Change 13mm 3 Jaw Keyless Chuck
- TSTAK kit box

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Tool Holder	SDS-Plus
Power Input	950 Watts
Voltage	0 V
Power Output	0 Watt
Impact energy (EPTA 05/2009)	3.5 J
No Load Speed	0-1150 rpm
Blows per Minute	0-5200 bpm
Max. Drilling Capacity [Concrete]	30 mm