



Product information

Weller®

WD1000MAU

Code No. : **WD1000MAU**



Multi-function digital soldering station with output up to 160 watts
Tool included is the WMRP 40 watt Micro soldering tool

Technical data

Voltage (heater):	230v
Heating output:	Max 160 w
Heat up time:	3 sec from ambient to 399°C
Temperature range:	50°C - 450°C
Temperature accuracy:	+/- 9°C
Temperature stability:	+/- 5°C
Connector:	Polarized, 5 pin locking
Tool Cord:	Silicone rubber, burn resistant
Sensor Type:	Integrated sensor / heater tip cartridge
Tip Type:	RT series for the WMRP
Dimensions WxDxH(mm):	134 x 108 x 147
Weight (kg)	4.3

Fast heat-up, thermal stability, and fine tips make it perfect for production or rework, in standard or lead-free applications
Heating element is built into the soldering tip for super-fast heat-up and recovery

Tool will automatically switch off when placed in the stand to extend tip life.

Micro processor allows programming of many features including temp offset, °C/ °F, set back time, temp lock to name a few.