



Main

Range	Mureva Styl
Range of product	Mureva Styl
Product or component type	Push-button
Category	Push-button
Device presentation	Complete product
Colour tint	Grey (RAL 7016)

Complementary

Device mounting	Surface
Switch function	Push-button
Actuator	Push-button
Rated current	10 A
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/Outdoor
Material	ABS (acrylonitrile butadiene-styrene) Brass SEBS
Fixing mode	Screwless
Clamping connection capacity	1.5...2.5 mm ² rigid 1.5...2.5 mm ² flexible 1.5...2.5 mm ² stranded
Wire stripping length	13 mm
Cable entry	Easy valve access Ø 6...20 mm
Length	76 mm
Height	64 mm
Width	76 mm
Embedding depth	0 mm
Projecting depth	64 mm

Environment

Quality labels	NF CE EAC
----------------	-----------------

AENOR

IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing ≥ 650 °C according to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C