



Product Datasheet

ENGLISH

**Stock No: 144-5341**

**Combustible Gas Leak Detector**

EN



# Specifications

<b>Visual Alert</b>	LCD liquid crystal display of flammable gas concentration of reading, Article Simulation Indications(fast and accurate).
<b>Audible Alert(85db)</b>	Loud Audible Ticking Rate(The sound frequency is directly proportional to the concentration of gas)
<b>Vibration Alert</b>	Standard
<b>Sensitivity</b>	<10ppm(methane)
<b>Response Time</b>	<2 Seconds
<b>Range</b>	Low concentration range 0-1000ppm(methane)High concentration range 0-10000ppm(methane)
<b>Warm Up Calibration</b>	Automatic
<b>Warm Up Time</b>	40 Seconds
<b>Operating Buttons</b>	Seven: Power ON/OFF, High/Low Sensitivity Audio Alerts, Vibration Alerts, Auto Zero,Auto Power Off, Back Light
<b>Batteries</b>	Polymer Li-Ion Battery
<b>Automatic shutdown</b>	Low power automatic shutdown and automatic shutdown for 10 minutes without operation.
<b>Sensor replacement</b>	Can replace
<b>Expected Sensor Life</b>	5 Years
<b>Probe</b>	Flexible 16"/400mm

## Features

- 1-LCD display
- 2-16" Adjustable Probe
- 3-Replaceable Sensor
- 4-TRI Mode Detection