

LOGO! 12/24RCEO, logic module, PS//O: 12/24VDC/relay, 8 DI (4AI)/4 DO, without display, Memory 400 blocks, modular expandable, Ethernet, integr. web server, data log, user-defined Web pages, standard microSD card for LOGO! Soft Comfort V8 or higher, older projects executable



Figure similar

Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide
Supply voltage	
Rated value (DC)	
• 12 V DC	Yes
• 24 V DC	Yes
permissible range, lower limit (DC)	10.8 V
permissible range, upper limit (DC)	28.8 V
Time of day	
Time switching clocks	
• Number	400; Max. 400, function-specific
• Power reserve	480 h
Digital inputs	
Number of digital inputs	8; Of which 4 can be used in analog mode (0 to 10 V)
Digital outputs	
Number of digital outputs	4; Relays

Short-circuit protection	No; external fusing necessary
Output current	
<ul style="list-style-type: none"> for signal "1" permissible range for 0 to 55 °C, max. 	10 A
Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	10 A
EMC	
Emission of radio interference acc. to EN 55 011	
<ul style="list-style-type: none"> Limit class B, for use in residential areas 	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
<ul style="list-style-type: none"> IP20 	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	Yes
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> min. 	-20 °C; No condensation
<ul style="list-style-type: none"> max. 	55 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> min. 	-40 °C
<ul style="list-style-type: none"> max. 	70 °C
Dimensions	
Width	71.5 mm
Height	90 mm
Depth	60 mm
last modified:	01/29/2018