



Specification TEK905 Decade Capacitance Box



Typical residual (zero) capacitance: < 40pF
Incremental accuracy: $\pm 5\%$ of setting at 1kHz
Maximum applied voltage: 100Vdc
Operating environment: 0°C to 50°C at < 70% RH
Dimensions: 345 x 71 x 51mm
Weight: 489g approx

Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Imperial Park, Imperial Way,
Watford, Hertfordshire, WD24 4PP, UK
Tel: +(0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk



©2012 Martindale Electric Company Ltd.
Registered in England No. 3387451. E. & O.E. Document Rev1 LIT905