

Datasheet
Stock No:1706970

RS Pro
ANTI-VIBRATION MMCX STRAIGHT EDGE MOUNT JACK RECEPTACLE

RECOMMENDED LAND PATTERN

APPROVED by DATE: _____

1.0 ELECTRICAL
 1.1 FREQUENCY RANGE: DC-17 GHz
 1.2 NOMINAL IMPEDANCE: 50 OHMS
 1.3 VOLTAGE RATING: 250 VOLTS MAX.
 1.4 VSWR: 1.22 MAX. @6 GHz

2.0 MATERIALS
 2.1 BODIES: BRASS PER JIS-C404
 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS
 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL
 4.1 INTERFACE IN ACCORDANCE WITH: RS EN 12240

5.0 ENVIRONMENTAL
 5.1 OPERATING TEMPERATURE RANGE: -55 C TO +155 C

NO	DESCRIPTION	MATERIAL	QTY	FINISH
4	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD 30µ" MIN.
3	INSULATION	TEFLON	1	NONE
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	GOLD 3µ" MIN.

DESCRIPTION	TOLERANCE	品名	40570208300017	日	DATE	版	REV.
Jackie	X ±0.2	TITLE	ROHS COMPLIANT (50Ω)	期	12.05.17	次	A-0
Arc	.XX ±0.1	單位	DWG.NO. 37-0096-Z				
Jenny	.XXX ±0.05	比例	SCALE				
	ANGLE ±5°	例	6:1				