

Hand Spot Welders

Spotmatic P2PT Hand spot Welder



[RS Stock No. 401-822](#)

Product Features

Fully adjustable tip pressure - for greater material & thickness versatility

Heavy duty transformer providing 2KVA @ 50% duty cycle

2mm of plate welding capacity - 60 spots/hour (mild steel) at 2 + 2 sheet

Superb welding speed - will weld 1.2mm sheet (mild steel) at (1.2 = 1.2) a rate of 260 spots/ hour

Electronic timer & compensation circuit

Specification:

SUPPLY	: 230v (20amp)
MAX. INPUT POWER	: 22.5KVA
OPEN CIRCUIT VOLTAGE	: 2.7v
MAX. WELD CURRENT	: 5750amps
MAX. WELD CAPACITY	: (mild steel) 2 + 2mm
MAX. LENGTH OF ARMS	: 96mm
ARM GAP	: 96mm
PROTECTION	: IP21
COMPENSATION CIRCUIT TIMER	: 0.05 to 1.25sec
WEIGHT	: 10.3kg
PACKAGED DIMENSIONS	: (H x W x L): 170 x 460 x 350mm
REPLACEMENT ELECTRODES	: 10mm Diameter - per pair Item No: 03275, Chrome Copper Alloy Bar 10mm Diameter x 750mm Item No: 03325

