

83 61 015

Pipe Wrench S-Type with fast adjustment



- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- Guard prevents operators' fingers being pinched
- Maximum load capability thanks to completely hardened handles
- High wear resistance due to the additionally hardened teeth
- Chrome vanadium electric steel, forged, multi stage oil-hardened



Article No.	83 61 015
EAN	4003773051923
Pliers	grey powder-coated
Handles	plastic coated
Clamping width mm	60
Capacities for pipes (diameter) Ø mm	60
Capacity for pipes, inches (diameter) Ø Inch	2 3/8
Inner diameter, inches Inch	1 1/2
Capacities for nuts mm	60
Inside dia. mm	37,5
Length mm	420
Net weight g	1470



technical change and errors excepted

