



mecalectro

Industrial Solenoid – 8.19.AB.83



Stroke: 16 mm

Force at beginning of stroke (FM: 100/25/5%):
6/20/55 N

Force at end of stroke (FM: 100/25/5%):
22/52/102 N

Power Consumption (FM: 100/25/5%):
18/65/310 W

Total mass: 600 g

Degree of protection / Energetic class: IP 40 / B

Standard supplies: 24Vcc

Possibles supplies: From 12 to 220Vcc

Duty Cycle: Permanent, impulsions (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: Automation, blocking, composting, distribution, stamping, punching.