



mecalectro

## Industrial Solenoid – 8.23D.01.85



**Stroke:** 25 mm

**Force at beginning of stroke (FM: 100/25/5%):**  
10/35/90 N

**Force at end of stroke (FM: 100/25/5%):**  
40/70/160 N

**Power Consumption (FM: 100/25/5%):**  
23/85/400 W

**Total mass:** 600 g

**Degree of protection / Energetic class:** IP 00 / B

**Standard supplies:** 230 Vac

**Possible supplies:** From 24 to 230 Vac

**Duty Cycle:** Permanent, impulses (100 / 40 / 25 / 15 / 5 %)

**Standard:** NF C 79300

**Examples of applications:** Automation, blocking, composting, distribution, stamping, punching.