


1727327
 1727328
 1727329
 1727331
 1727332
 1727333
 1727334
 1727335

Din Rail box loaded 12 x SC Simplex
 Din Rail box loaded 12 x SC
 Din Rail box loaded with 6 x LC
 Din Rail box loaded with 6 x LC
 Din Rail box loaded with 12 x ST
 Din Rail box loaded with 12 x ST
 Din Rail box loaded with 12 x FC
 Din Rail box loaded with 12 x FC Multi

Din Rail Demarcation Box



Our Din Rail splice box offers a wide range of flexibility to the end user. The standard enclosure includes a hinged splice holder house up to 12 splice protectors, and 1 cable gland for incoming.

- 
- Din Rail mounting
 - Top and bottom cable entry points (1 x Cable gland Included)
 - Strength member tie position x 1
 - Splice Holder for 12 splice protectors or splice holder for 12 metal crimp splice protectors
 - Suitable for pre-terminated cables, splicing, or pass through
 - IP20
 - Internal application
 - Data Centre or telecommunications networks
 - For use in multi dwelling units or demarcation points within a network



Height	110mm
Width	60mm
Depth	113mm
Net weight	522g
Packaged weight	579g
Packaged dimensions	157mm x 122mm x 67mm
Suitable for adapter type	ST, FC, SC Simplex, LC Duplex, E2000
Number of fibers	Up to 12 fibers
Material	Cold-rolled steel
Material thickness	1.5mm
Material coating	Powder coating
Material coating	Grey RAL 7035
Colour	-40°C to +60°C
Operating temperature	TIA/EIA 568.C, ISO/IEC 11801, EN50173, IEC60304,
Designed in accordance with Compliant to	IEC61754, RoHS, Reach/SVHC

TECHNICAL DRAWING

