

HEADLIGHT FUTURE



ANSMANN High Performance Headlight Future

Description:

The High quality ANSMANN FUTURE water proof headlight includes a 1.8W LED which can be adjusted up to 70° and comes with a reflective headband for maximum visibility of the wearer.

This product is supplied with 3x ANSMANN AAA batteries and is comfortable to wear weighing in at only 45g.

The Headlight FUTURE has two settings, 100% and 30% brightness.

The illumination intensity is 4000 (100%) / 1600 (30%) Lux, and has a range of approximately 200m.

The operating time is 6 hours continued use at 100% and 15 hours at 30%.

This headlight FUTURE diffuses light, giving a much wider beam. This makes it just as good for close up work as for outdoor use.

This product is supplied with a **3 year warranty**.

INFORMATION

Product name: Headlight Future
Article nummer: 1600-0044
EAN-Code: 4013674023042
Accessories incl.: 3x Alkaline Micro AAA batteries

Product weight: 45g (incl. Batteries)
Packing unit: 4