

56881

Bucket, 260 mm, , Pink



This durable 6 litres bucket is suitable for cleaning or storage of ingredients and food stuff. The bucket has a wide drip-free spout, sturdy stainless steel hanger, hand grip at the bottom that is raised from the base and calibrated for a variety of measuring units. The flat side prevents spillage and it has its own wall bracket, 16200 for storage.

# Technical Data

<b>Item Number</b>	56881
<b>Volume</b>	6 Litre(s)
<b>Material</b>	Polypropylene Stainless Steel
<b>Suitable for Food Contact (EU 1935/2004), DoC <sup>1</sup></b>	Yes
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes
<b>Use of Phthalates (e.g. Bisphenol A)</b>	No
<b>Is Halal compliant</b>	Yes
<b>Box Quantity</b>	5 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	160 Pcs
<b>Quantity Per Layer (Pallet)</b>	40 Pcs.
<b>Box Length</b>	295 mm
<b>Box Width</b>	275 mm
<b>Box Height</b>	430 mm
<b>Length</b>	260 mm
<b>Width</b>	270 mm
<b>Height</b>	258 mm
<b>Gross Weight</b>	0,61 kg
<b>Net Weight</b>	0,55 kg
<b>Cubik metre</b>	0,0181 M3
<b>Recommended sterilisation temperature (Autoclave)</b>	121 °C
<b>Max. cleaning temperature (Dishwasher)</b>	93 °C
<b>Max usage temperature (food contact)</b>	100 °C
<b>Max usage temperature (non food contact)</b>	100 °C
<b>Min. usage temperature</b>	-20 °C
<b>Max. drying temperature</b>	120 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	10,5 pH
<b>Gtin-13 Number</b>	5705020568817
<b>GTIN-14 Number (Box quantity)</b>	15705020568814
<b>Commodity Code</b>	39233090
<b>Country of origin</b>	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact