

31742

# Broom, 410 mm, Soft/hard, Green



This sweeping broom has two types of bristles. When pushing the broom forward the front rows, which have firm bristles, loosen the dirt and push heavier debris. The softer bristles of the back rows, gather the finer particles. It is suitable for all areas in kitchens and restaurants.

# Technical Data

Item Number	31742
Visible bristle length	52 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC <sup>1</sup>	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	480 Pcs
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	545 mm
Box Width	270 mm
Box Height	220 mm
Length	410 mm
Width	90 mm
Height	120 mm
Gross Weight	0,584 kg
Net Weight	0,548 kg
Cubik metre	0,0044 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020317422
GTIN-14 Number (Box quantity)	15705020317429
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.