

53783

Tube Brush, 510 mm, Hard, Blue



The 40mmø of this tube cleaners is used to clean small pipes and very narrow spaces between machine parts. The filaments are attached to a twisted stainless steel rod which makes chemical resistant and strong.

Technical Data

Item Number	53783
Visible bristle length	17 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	480 Pcs
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	530 mm
Box Width	230 mm
Box Height	155 mm
Product Diameter	40 mm
Length	510 mm
Width	40 mm
Height	40 mm
Gross Weight	0,098 kg
Net Weight	0,08 kg
Cubik metre	0,0008 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020537837
GTIN-14 Number (Box quantity)	15705020537834
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact