

56733

Hand shovel, 327 x 271 x 50
mm, 550 mm, Blue



Lightweight and durable hand shovel. Its one piece construction eliminates areas where bacteria can be harboured. Smooth surface makes it extremely easy to clean, ideal for use in food production areas for moving food ingredients or large quantities of food waste.

Technical Data

| | |
|---|-------------------|
| Item Number | 56733 |
| Shovel Blade Size, L x W x H | 327 x 271 x 50 mm |
| Material | Polypropylene |
| Suitable for Food Contact (EU 1935/2004), ¹ | Yes |
| Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice | Yes |
| FDA compliant raw material (CFR 21) | Yes |
| Meets the REACH Regulation (EC) No. 1907/2006 | Yes |
| Use of Phthalates (e.g. Bisphenol A) | No |
| Is Halal compliant | Yes |
| Box Quantity | 12 Pcs. |
| Quantity per Pallet (80 x 120 x 200 cm) | 240 Pcs. |
| Quantity Per Layer (Pallet) | 48 Pcs. |
| Box Length | 600 mm |
| Box Width | 335 mm |
| Box Height | 320 mm |
| Length | 550 mm |
| Width | 275 mm |
| Height | 110 mm |
| Gross Weight | 0,545 kg |
| Net Weight | 0,509 kg |
| Cubik metre | 0,0166 M3 |
| Recommended sterilisation temperature (Autoclave) | 121 °C |
| Max. cleaning temperature (Dishwasher) | 93 °C |
| Max. usage temperature (for food contact) | 100 °C |
| Max usage temperature (non food contact) | 100 °C |
| Min. usage temperature | -20 °C |
| Max. drying temperature | 120 °C |
| Min. pH-value in usage concentration | 2 pH |
| Max. pH-value in Usage Concentration | 10,5 pH |
| Recycling Mark 7 | Yes |
| GTIN-13 Number | 5705020567339 |
| GTIN-14 Number (Box quantity) | 15705020567336 |
| Commodity Code | 39241000 |
| Country of origin | Denmark |

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact