



# Datasheet

# COB LED 250 LM

# Worklight with Strong

# Magnet

RSPRO-i1  
1766026





<b>LED:</b>	COB LED
<b>Lumen:</b>	250 Lumen
<b>Wattage:</b>	5W
<b>Colour Temp:</b>	6500k
<b>Operating Voltage:</b>	4.5v
<b>IP Rating:</b>	IPX4
<b>Anti-Corrosive:</b>	No

### **Features:**

Black high-end aluminium construction  
Tactical rubberised operation switch  
Functioned by 3 x AAA Batteries  
Pocket clip attached on reverse  
Strong magnet on base  
IPX4 Water Resistance  
Contoured Operation Grips

**Dimensions:** 154 x 15 x 15mm

**Batteries:** 3 x AAA Alkaline (included)

**Weight:** 55.5g Torch Only, 91g with batteries installed

### **Switching Modes:**

High ON / Low ON / Red Flash / OFF

### **ANSI FL1 Standard**

Lumens: 100% - 250 lumen / 30% - 90 lumen

Runtime: 100% - 3H / 30% - 8H / Red - 10H

Beam Range: 100% - 25m / 30% - 17m