



Datasheet

COB LED 400 LM Work light with Strong Magnet

RSPRO-i2
1766027





LED:	COB LED
Lumen:	400 Lumen
Wattage:	5W
Colour Temp:	6200k
Operating Voltage:	4.5v
IP Rating:	IPX4
Anti-Corrosive:	No

Features:

Black high-end aluminium construction
Tactical rubberised operation switch
Functioned by 3 x AA Batteries
Strong magnet on base
IPX4 Water Resistance

Dimensions: 192 x 25 x 25mm

Batteries: 3 x AA Alkaline (included)

Weight: 137g torch only, 211g with batteries

Switching Modes:

High ON / Low ON / Red Flash / OFF

ANSI FL1 Standard

Lumens: 100% - 400 lumen / 30% - 160 lumen

Runtime: 100% - 4.5H / 30% - 15H / Red Flash - 40H

Beam Range: 100% - 29m / 30% - 18m