

# NEW DRILL & TAP DUO PACK!

- Totally NEW 2pc set featuring tap & pre-hole drill in one convenient package
- Brand new packaging concept features Twist-Lock closure and transparent lid with euroslot hanger making it ideal for retail display
- Features the A002 split-point jobber drill and a choice of popular taps
- Options include straight flute hand taps and DIN or ISO spiral point and spiral flute machine taps
- Available in different size combinations:
  - M3+2.5mm
  - M4+3.3mm
  - M5+4.2mm
  - M6+5.0mm
  - M8+6.8mm
  - M10+8.5mm
  - M12+10.2mm(see over for full range info)

Makes  
selection  
of tap & correct  
pre-hole drill  
simple!




#### Options available:

All with A002 HSS TiN coated jobber drill

- L000: E500 HSS straight flute tap for threading through or blind holes up to 1.5xD in most materials (ISO standard)
- L001: EP006H/EX006H HSS-E spiral point/spiral flute 45° taps for threading up to 2.5xD in most materials (DIN standard)
- L002: E000/E002 HSS-E spiral point/spiral flute 45° taps for threading up to 2.5xD in most materials (ISO standard)


# L000

## ● Hand Tap-Drill Set (2 Piece)

L000	Nr.	A	B	M	D	L000
	Nr.1	E500 + A002	2	E500M3NO2	A0022.5	L000E500M3NO2XA002
	Nr.2	E500 + A002	2	E500M4NO2	A0023.3	L000E500M4NO2XA002
	Nr.3	E500 + A002	2	E500M5NO2	A0024.2	L000E500M5NO2XA002
	Nr.4	E500 + A002	2	E500M6NO2	A0025.0	L000E500M6NO2XA002
	Nr.5	E500 + A002	2	E500M8NO2	A0026.8	L000E500M8NO2XA002
	Nr.6	E500 + A002	2	E500M10NO2	A0028.5	L000E500M10NO2XA002
	Nr.7	E500 + A002	2	E500M12NO2	A00210.2	L000E500M12NO2XA002
	Nr.8	E500 + A002	2	E500M3NO3	A0022.5	L000E500M3NO3XA002
	Nr.9	E500 + A002	2	E500M4NO3	A0023.3	L000E500M4NO3XA002
	Nr.10	E500 + A002	2	E500M5NO3	A0024.2	L000E500M5NO3XA002
	Nr.11	E500 + A002	2	E500M6NO3	A0025.0	L000E500M6NO3XA002
	Nr.12	E500 + A002	2	E500M8NO3	A0026.8	L000E500M8NO3XA002
	Nr.13	E500 + A002	2	E500M10NO3	A0028.5	L000E500M10NO3XA002
	Nr.14	E500 + A002	2	E500M12NO3	A00210.2	L000E500M12NO3XA002


# L001

## ● DIN Tap-Drill Set (2 Piece)

L001	Nr.	A	B	M	D	L001
	Nr.1	EP006H + A002	2	EP00M3	A0022.5	L001EP00M3XA002
	Nr.2	EP006H + A002	2	EP00M4	A0023.3	L001EP00M4XA002
	Nr.3	EP006H + A002	2	EP00M5	A0024.2	L001EP00M5XA002
	Nr.4	EP006H + A002	2	EP00M6	A0025.0	L001EP00M6XA002
	Nr.5	EP006H + A002	2	EP00M8	A0026.8	L001EP00M8XA002
	Nr.6	EP006H + A002	2	EP00M10	A0028.5	L001EP00M10XA002
	Nr.7	EP006H + A002	2	EP00M12	A00210.2	L001EP00M12XA002
	Nr.8	EX006H + A002	2	EX00M3	A0022.5	L001EX00M3XA002
	Nr.9	EX006H + A002	2	EX00M4	A0023.3	L001EX00M4XA002
	Nr.10	EX006H + A002	2	EX00M5	A0024.2	L001EX00M5XA002
	Nr.11	EX006H + A002	2	EX00M6	A0025.0	L001EX00M6XA002
	Nr.12	EX006H + A002	2	EX00M8	A0026.8	L001EX00M8XA002
	Nr.13	EX006H + A002	2	EX00M10	A0028.5	L001EX00M10XA002
	Nr.14	EX006H + A002	2	EX00M12	A00210.2	L001EX00M12XA002

# L002

## ● ISO Tap-Drill Set (2 Piece)

L002	Nr.	A	B	M	D	L002
	Nr.1	E000 + A002	2	E000M3	A0022.5	L002E000M3XA002
	Nr.2	E000 + A002	2	E000M4	A0023.3	L002E000M4XA002
	Nr.3	E000 + A002	2	E000M5	A0024.2	L002E000M5XA002
	Nr.4	E000 + A002	2	E000M6	A0025.0	L002E000M6XA002
	Nr.5	E000 + A002	2	E000M8	A0026.8	L002E000M8XA002
	Nr.6	E000 + A002	2	E000M10	A0028.5	L002E000M10XA002
	Nr.7	E000 + A002	2	E000M12	A00210.2	L002E000M12XA002
	Nr.8	E002 + A002	2	E002M3	A0022.5	L002E002M3XA002
	Nr.9	E002 + A002	2	E002M4	A0023.3	L002E002M4XA002
	Nr.10	E002 + A002	2	E002M5	A0024.2	L002E002M5XA002
	Nr.11	E002 + A002	2	E002M6	A0025.0	L002E002M6XA002
	Nr.12	E002 + A002	2	E002M8	A0026.8	L002E002M8XA002
	Nr.13	E002 + A002	2	E002M10	A0028.5	L002E002M10XA002
	Nr.14	E002 + A002	2	E002M12	A00210.2	L002E002M12XA002

A= Styles in Set, B= No. in Set, M= Tap diameters in Set, D= Drill diameters in Set