

# R2.5-10VSC-H



Ring Terminal max 2.5SQMM M10



## General Information

Extended Product Type	R2.5-10VSC-H
Product ID	7TBA301300R0093
EAN	5415022400243
Catalog Description	Ring Terminal max 2.5SQMM M10
Long Description	Vinyl-Insulated Ring Terminal, Single Crimp, Length 30.5mm, Width 13.6mm, Diameter 4.8mm, Stud Size M10, Wire Range 1.5-2.5mm <sup>2</sup> , Copper, Tin Plated, Temperature Range -30 to 75 Degrees C, 600V Max, Color Blue

## Ordering

EAN	5415022400243
Minimum Order Quantity	8750 piece
Customs Tariff Number	8536904000

## Dimensions

Product Net Weight	0.907 g
--------------------	---------

## Container Information

Package Level 1 Width	25.4 mm
Package Level 1 Height	101.6 mm
Package Level 1 Depth / Length	152.4 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	152.4 mm
Package Level 2 Height	88.9 mm
Package Level 2 Depth / Length	177.8 mm
Package Level 3 Units	5000 piece
Package Level 3 Width	317.5 mm
Package Level 3 Height	203.2 mm
Package Level 3 Depth / Length	482.6 mm

## Additional Information

Brand / Label	Spec-Kon
Color	Blue

Material	Copper
Product Main Type	COMPRESSION TERMINALS
Product Name	Electrical Wiring Terminal
Product Type	Vinyl-Insulated Ring Terminal
UPC	786210134888

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	R2.5-10VSC-H
Instructions and Manuals	R2.5-10VSC-H

---

### Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

---

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

