

MBD2.5-4NDC-H



Male Bullet 2.5SQMM DC



General Information

Extended Product Type	MBD2.5-4NDC-H
Product ID	7TBA301100R0070
EAN	5415022400809
Catalog Description	Male Bullet 2.5SQMM DC
Long Description	Nylon-Insulated Male Bullet Disconnect, Double Crimp, Length 21.7mm, Width 4mm, Diameter 4.7mm, Wire Range 1.5-2.5mm ² , Brass, Tin Plated, Temperature Range -30 to 105 Degrees C, 600V Max, Color Blue

Ordering

EAN	5415022400809
Minimum Order Quantity	20000 piece
Customs Tariff Number	8536908585

Dimensions

Product Net Weight	0.907 g
--------------------	---------

Container Information

Package Level 1 Width	25.4 mm
Package Level 1 Height	101.6 mm
Package Level 1 Depth / Length	152.4 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	152.4 mm
Package Level 2 Height	88.9 mm
Package Level 2 Depth / Length	177.8 mm
Package Level 3 Units	10000 piece
Package Level 3 Width	317.5 mm
Package Level 3 Height	203.2 mm
Package Level 3 Depth / Length	482.6 mm

Additional Information

Brand / Label	Spec-Kon
Color	Blue
Material	Brass

Product Main Type	COMPRESSION TERMINALS
Product Name	ELECTRICAL WIRING TERMINAL
Product Type	Nylon-Insulated Female Bullet Disconnect
UPC	786210135472

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	MBD2.5-4NDC-H
Instructions and Manuals	MBD2.5-4NDC-H

Classifications

ETIM 6	EC000516 - Round or flat plug/receptacle
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

