

4-Port USB Hub - Metal - USB-A to 3x USB-A and 1x USB-C - USB 3.0

Product ID: HB30A3A1CST



This 4-port USB 3.0 hub turns your laptop or desktop USB-A port into two standard USB-A ports, one USB-A fast-charge port and one USB-C™ port. You can also extend the range of your USB devices by using this hub as a mid-point repeater.

Connect more devices quickly and easily

The 4-port hub is designed for easy port access, when the hub is mounted or sitting on your desk. The hub ports are spaced with enough room between them to easily plug or unplug your USB devices, without having to disconnect other devices from neighboring ports.

With extra USB 3.0 ports, you can increase productivity and connect more devices to your computer, or simply avoid the hassle of swapping connected devices on your port-limited laptop. The USB-C port is ideal for connecting new USB-C devices, like an external USB-C drive, to a traditional USB-A port on your computer.

It's perfect for IT professionals or anyone who needs to plug and unplug their devices regularly.

Enjoy mounted or desktop convenience

This hub is perfect the perfect accessory for a laptop or desktop workstation, with a rugged metal housing that can withstand the wear and tear of daily use.

With the included wall-mount bracket, you can attach the hub to a surface such as a desktop or wall, to better suit your needs.

Charge-and-sync your mobile devices

With the available fast-charge port, the hub helps to ensure that your tablet or smartphone are charged and ready to use when you need them. You can also sync and access your device while it is charging. The USB-A charge port supports USB Battery Charging Specification 1.2 and delivers up to 2.4 amps of power, so you can charge your mobile device faster than traditional USB ports allow.

The HB30A3A1CST is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Installation in locations where USB 3.0 ports need to be securely mounted to a surface, such as a wall or under a desk
- Upgrade and expand the connection capabilities of your MacBook, Ultrabook, laptop, or desktop
- Deploy in hot desk environments to provide USB hub access for multiple devices

Features

- Flexible mounting options, with the included desktop or wall-mount bracket
- Connect a USB-C peripheral device through a traditional USB-A port
- Add both USB-C and USB-A ports to your USB-A port equipped laptop, MacBook, Chromebook™, or desktop computer
- Supports USB Battery Charging Specification 1.2 and delivers up to 2.4 amps through the USB-A charge port
- USB-A ports are backward compatible with older USB 2.0 and 1.1 devices
- Industrial, metal enclosure
- Integrated physical On/Off power button
- Plug-and-play, and supports hot-swapping or hot-plugging
- All ports are compliant with USB 3.0 and data rates up to 5Gbps

Hardware	Warranty	2 Years	
	Bus Type	USB 3.0	
	Chipset ID	Realtek - RTS5411	
	Fast-Charge Port(s)	Yes	
	Industry Standards	USB Battery Charging Specification Rev. 1.2 USB-A charging port delivers up to 2.4 amps of power USB 3.0 - Backward compatible with USB 2.0 and 1.1	
	Interface	USB 3.0	
	Ports	4	
	USB-C Device Port(s)	Yes	
	USB-C Host Connection	No	
Performance	Maximum Data Transfer Rate	5 Gbps	
	Type and Rate	USB 3.0 - 5 Gbit/s	
Connector(s)	Connector Type(s)	2 - USB Type-A (9 pin) USB 3.0 Female 1 - USB Type-C (24 pin) USB 3.0 Female 1 - USB 3.0 A (Fast-Charge, 9 pin, SuperSpeed) Female 1 - USB Type-B (9 pin) USB 3.0 Female	
	OS Compatibility	OS Independent; No additional drivers or software required	
	Special Notes / Requirements	Note	The USB Type-C port is data only. USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. The hub does not support DP Alt Mode or USB Power Delivery.
		System and Cable Requirements	Available USB Type-A ports - USB 3.0 (5Gbps)
Indicators	LED Indicators	1 - Power 4 - Hub Port Connection	
	Power	Center Tip Polarity	Positive
Input Current		0.6 A	
Input Voltage		100 ~ 240 AC	
Output Current		2A	
Output Voltage		12 DC	
Plug Type		M	
Power Consumption (In Watts)		24	
Power Source		AC Adapter Included	

Environmental	Humidity	20~80% RH (Non-condensing)
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 50°C (-4°F to 122°F)
Physical Characteristics	Cable Length	39.4 in [1000 mm]
	Color	Black
	Enclosure Type	Aluminum
	Form Factor	Desktop
	Product Height	0.9 in [24 mm]
	Product Length	3.9 in [100 mm]
	Product Weight	4.8 oz [135 g]
	Product Width	2.4 in [60 mm]
Packaging Information	Shipping (Package) Weight	18.9 oz [535 g]
What's in the Box	Included in Package	1 - USB 3.0 hub
		1 - universal power adapter (NA/JP, UK, EU, ANZ)
		1 - USB-A to USB-B cable
		2 - rubber feet
		2 - mounting brackets
		4 - mounting screws
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.