



Main

Range	Acti 9
Product or component type	Earth leakage add-on block
Device short name	Vigi iC65 ELE
Poles description	4P
[In] rated current	63 A
Network type	AC
Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V AC 50/60 Hz
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Class AC
9 mm pitches	7

Complementary

Residual current tripping technology	Voltage dependent
[Ui] rated insulation voltage	500 V AC
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-2
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws
Height	101 mm
Width	63 mm
Depth	73.5 mm
Connections - terminals	Tunnel type terminals bottom connection rigid Tunnel type terminals bottom connection flexible without cable end Tunnel type terminals bottom connection flexible with cable end
Tightening torque	Power circuit : 3.5 N.m

Environment

Product certifications	CCC
IP degree of protection	In open air: IP20 conforming to GB 4208 In enclosure: IP40 conforming to GB 4208
Pollution degree	3 conforming to IEC 60947-2
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C