


Cross Recess Countersunk Twin Thread



BZP

No. 4 x 1/2in	144-3495
No. 4 x 5/8in	144-3496
No. 4 x 3/4in	144-3497
No. 4 x 1in	144-3498
No. 6 x 1/2in	144-3499
No. 6 x 5/8in	144-3500
No. 6 x 3/4in	529-062
No. 6 x 1	529-078
No. 6 x 1.1/4	529-084
No. 6 x 1.1/2	529-090
No. 8 x 1/2	521-169
No. 8 x 5/8	144-3501
No. 8 x 3/4	521-181
No. 8 x 1	529-107
No. 8 x 1.1/4	529-113
No. 8 x 1.1/2	529-129
No. 8 x 1.3/4	521-197
No. 8 x 2	529-135
No. 8 x 2.1/2	521-204
No. 8 x 3	144-3502
No. 10 x 1	529-141
No. 10 x 1.1/4	521-226
No. 10 x 1.1/2	529-157
No. 10 x 1.3/4	521-232
No. 10 x 2	529-163
No. 10 x 2.1/2	529-179
No. 10 x 3	521-248
No. 10 x 3.1/2	144-3503
No. 10 x 4	144-3504
No. 12 x 1.1/2	144-3505
No. 12 x 2	521-254
No. 12 x 2.1/2	144-3506
No. 12 x 3	521-260
No. 12 x 4	521-282

	Cross Recess Countersunk General Purpose		Cross Recess Round Single Thread DIN 7996	Cross Recess Countersunk Single Thread DIN 7997	Slot Round Single Thread DIN 96	Slot Countersunk Single Thread DIN 97	Ulti-Mate Pozisquare Countersunk High Performance	Unifix Vortex Recessed Countersunk High Performance
	Zinc Plated, Yellow Passivated	A2	A2	A2	A2	A2	Zinc Plated, Yellow Passivated	Zinc Plated, Yellow Passivated
3 x 12mm	263-1808							
3 x 16mm	144-3470			144-3524				
3 x 20mm	144-3471			144-3525				
3 x 25mm	263-1814			144-3526				
3.5 X 12mm	144-3472							
3.5 x 16mm	263-1820			144-3527				145-6460
3.5 x 20mm	144-3473	144-3507	483-3012	483-3090		483-3056		145-6461
3.5 x 25mm	263-1836	144-3508		483-3113				145-6462
3.5 x 30mm		144-3509		483-3129				145-6463
3.5 x 40mm	263-1842							145-6464
3.5 X 45mm	144-3474							
3.5 X 50mm	144-3475							
4 x 20mm				483-3135	483-2867	144-3530		145-6465
4 x 25mm	263-1858	797-6229	483-3220	483-3141	483-2873	483-3062	493-4553	145-6466
4 X 30mm	144-3476	797-6222	144-3517	483-3157	483-2889	144-3531	493-4569	145-6467
4 X 35mm	144-3477							
4 x 40mm	263-1864	797-6226	483-3236	483-3006	483-2895	483-3078	493-4575	145-6468
4 X 45mm	144-3478							
4 x 50mm	263-1870	797-6235	144-3518	483-3163	483-2902		493-4581	145-6469
4 X 60mm	144-3479	144-3510						145-6470
4 x 70mm							493-4597	145-6471
4.5 x 25mm	263-1892							
4.5 X 30mm	144-3480							
4.5 X 35mm	144-3481							

	Cross Recess Countersunk General Purpose		Cross Recess Round Single Thread DIN 7996	Cross Recess Countersunk Single Thread DIN 7997	Slot Round Single Thread DIN 96	Slot Countersunk Single Thread DIN 97	Ulti-Mate Pozisquare Countersunk High Performance	Unifix Vortex Recessed Countersunk High Performance
	Zinc Plated, Yellow Passivated	A2	A2	A2	A2	A2	Zinc Plated, Yellow Passivated	Zinc Plated, Yellow Passivated
4.5 x 40mm	263-1909							
4.5 X 50mm	144-3482							145-6472
4.5 X 60mm	144-3483							145-6473
4.5 x 70mm	263-1915							145-6474
5 x 25mm			144-3519	483-3179		483-2918		
5 x 30mm	263-1921	144-3511	144-3520	483-3185		483-2924		
5 x 40mm	263-1937	797-6238	483-3242	483-3191	483-3084	483-2930		145-6475
5 X 50mm	144-3484	797-6232	144-3521	483-3208		483-2946	493-4604	145-6476
5 X 60mm	144-3485	797-6241						145-6477
5 x 65mm			144-3522	483-3214		483-3034		
5 x 70mm	263-1959	797-6244					493-4610	145-6478
5 X 75mm	144-3486		144-3523	144-3528				
5 X 80mm	144-3487	144-3512					493-4626	145-6479
5 X 90mm	144-3488							145-6480
5 X 100mm	144-3489	144-3513		144-3529				145-6481
6 x 40mm	263-1965							
6 X 50mm	144-3490						493-4648	145-6482
6 X 60mm	144-3491	144-3514						145-6483
6 x 70mm	263-1971	797-6248					493-4654	
6 X 80mm	144-3492	144-3515						145-6484
6 X 90mm	144-3493							
6 X 100mm	144-3494	144-3516					493-4660	145-6485
6 x 120mm								145-6486