

- Part number: TRW 14027
- Description : Complet set of 1/4" ratchet wrench
- Square drive : 1/4"
- Maxi torque : 27 N/m
- Air consumption : 103 l/min.
- Rotation speed : 200 rpm (unloaded)
- Inlet thread : 1/4" BSPF
- Hose ID : 10 mm (3/8")
- Working pressure : 6,3 bar
- Niveau sonore : dBa
- Vibrations : m/s<sup>2</sup>
- Length : 135 mm
- Weight : 0,5 kg
- Material : Composite body, aluminium head
- Trigger : Progressive
- Benefits : Heavy duty, light, easy
- Included : 5 sockets (8, 9, 10, 11, 12)
- Included : Swiveling connection
- Included : 2 extensions (50, 100 mm)



## Applications



PREVOST SAS – C.S. 90208 - 74942 ANNECY-LE-VIEUX CEDEX - France

Tel. +33 (0)4 50 64 04 45 - Fax. +33 (0)4 50 64 00 10 - sales@prevost.eu - [www.prevost.eu](http://www.prevost.eu)

Ce document ne peut être considéré comme contractuel. Dans un souci d'apporter un meilleur service à ses clients, la société PREVOST se réserve la possibilité de modifier les caractéristiques de sa gamme, sans préavis