

## 2 Port USB DVI KVM Switch with Audio and Cables

Product ID: SV211KDVIGB



This USB DVI KVM Switch provides access and control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching that allows an uninterrupted audio experience, even when switching back and forth between computers.

The perfect KVM switch for multimedia applications, SV211KDVIGB supports both digital and analog video signal transmissions for display resolutions of up to 1900x1200 (digital) and 2048x1536 (analog). The switch also features an integrated USB 2.0 hub that allows you to share two high-speed USB devices between computers.

Compatible with Mac, Linux or PC Based computers, the DVI KVM switch (SV211KDVIGB) is a great addition for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production workstations and more, and features a compact form factor design that helps preserve valuable desk space.

A complete, out-of-the-box solution, this DVI KVM Switch (SV211KDVIGB) includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate the cable clutter that could result from using multiple cables.

### Certifications, Reports and Compatibility



### Applications

- Ideal for desktops, workstations and servers with Flat Panel LCD monitors.
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required.
- Sharing computers and USB devices in the home/SOHO/multimedia environment/

### Features

- Compact design saves space
- Compatible with all USB supported Operating Systems.
- Computer selection by push button, keyboard hotkeys and Switching Software(for Windows/Mac)
- Designed for high-resolution applications: 1920 x 1200 digital resolution and 2048 x 1536 analog resolution
- Hot Pluggable - add or remove computers without having to power down the switch
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- LED indicators for easy status monitoring.
- USB 2.0/1.1 specification compliant.
- HDCP Compliant

<b>Hardware</b>	Warranty	2 Years
	Audio	Yes
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	DVI
Rack-Mountable	No	
<b>Performance</b>	DVI Support	Yes
	Hot-Key Selection	Yes
	IP Control	No
	Maximum Analog Resolutions	2048x1536
	Maximum Digital Resolutions	1920x1200
	Maximum Number of Users	1
	On-Screen Display	No
Port Selection Support	Push Button and Hotkeys	
<b>Connector(s)</b>	Console Interface(s)	1 - DVI-I (29 pin) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	2 - DVI-I (29 pin) Female 2 - USB B (4 pin) Female
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.4A
	Input Voltage	110V-240V AC
	Output Current	2A
	Output Voltage	5 DC
	Plug Type	N
	Power Consumption (In Watts)	10
Power Source	AC Adapter Included	

<b>Physical Characteristics</b>	Color	White
	Enclosure Type	Plastic
	Product Depth	65.5 mm [2.6 in]
	Product Height	27 mm [1.1 in]
	Product Weight	160 g [5.6 oz]
	Product Width	154 mm [6.1 in]
<b>Packaging Information</b>	Shipping (Package) Weight	1.3 kg [2.8 lb]
<b>What's in the Box</b>	Included in Package	1 - 2 Port KVM
		2 - 4 ft. DVI/Audio&Mic combo cables
		2 - 4 ft. USB cables
		1 - Power Adapter
		1 - Software CD

Product appearance and specifications are subject to change without notice.