

## 4 Port Professional VGA USB KVM Switch with Hub

Product ID: SV431USB

The SV431USB 4 Port rack mountable VGA USB KVM Switch with Hub offers simple control of up to four computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The USB KVM switch features an integrated 4 port USB hub, allowing you to share connected USB peripherals between the four controlled PC/Mac computers as though the devices were connected directly.

Offering convenient placement and installation options, the KVM switch features a 1U rack-mountable form factor and rear port connection to master and slave computers, allowing you to make the necessary device connections without disrupting your workspace.

A cross-platform solution, the KVM switch supports high resolution applications at up to 1920x1440 and provides a smooth operating experience when controlling mixed (Windows/Mac OS/Linux) environments.

This product is TAA compliant and backed by a Startech.com 3 year warranty with free lifetime technical support.

### Rackmount your KVM switch

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

### Certifications, Reports and Compatibility



### Applications

- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice
- Dual system control for single user workstations increasing user productivity in the office

### Features

- Supports hot-plug and disconnect – computers can be added or removed without the need to reboot other connected systems
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets
- Front panel push-buttons for quick and easy switching
- High 1920x1440 resolution capability
- OS independent - No driver or software installation required
- USB 2.0 hub for peripheral sharing
- USB self-power operation

<b>Hardware</b>	Warranty	3 Years
	Audio	No
	Cables Included	No
	Daisy-Chain	No
	KVM Ports	4
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	Optional
	U Height	1U
<b>Performance</b>	Auto Scan	3, 8, 15 & 30 seconds
	DVI Support	No
	Hot-Key Selection	No
	IP Control	No
	Maximum Analog Resolutions	1920 x 1440
	Maximum Cable Length	16.4 ft [5 m]
	Maximum Number of Users	1
	MTBF	82506 hours
	On-Screen Display	No
	Port Selection Support	Push Button
<b>Connector(s)</b>	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 4 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	4 - USB B (4 pin) Female 4 - VGA (15 pin, High Density D-Sub) Male
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>	<b>Note</b>	In order to use the SV431USB with a USB keyboard that has additional USB ports, such as an Apple Macintosh keyboard, or to use the SV431USB with a USB hub, an additional power supply may be required
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.4A
	Input Voltage	110V-240V AC
	Output Current	2A

	Output Voltage	5 DC
	Plug Type	N
	Power Source	Not Included (not required for standard applications)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Product Height	1.7 in [44 mm]
	Product Length	8.7 in [220 mm]
	Product Weight	34.9 oz [988 g]
	Product Width	5.1 in [130 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	2.8 lb [1.3 kg]
<b>What's in the Box</b>	Included in Package	1 - 4 Port VGA USB KVM Switch
		4 - Rubber Feet
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.