

4 Port Black USB KVM Switch Kit with Cables and Audio

Product ID: SV411KUSB

The SV411KUSB 4 Port USB KVM Switch Kit with Audio and Cables lets you control up to four USB-enabled computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the USB KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the USB KVM switch supports video resolutions of up to 2048 x 1536 as well as audio switching. The USB KVM switch includes four, 4ft 4-in-1 VGA and USB Host Cables, providing everything needed for quick installation to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control 4 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Applicable for call centers, help desks, education environments, home gamers, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Multiple system control for single user workstations, increasing user productivity in the office

Features

- Cables (4 ft.) included
- Includes audio support for a complete switching solution
- Maximum resolution: 2048 x 1536
- Switching type: Hotkey, push-button

Hardware	Warranty	2 Years
	Audio	Yes
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	4
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	No
Performance	DVI Support	No
	Hot-Key Selection	Yes
	IP Control	No
	Maximum Analog Resolutions	2048 x 1536 pixels
	Maximum Number of Users	1
	On-Screen Display	No
	Port Selection Support	Push Button and Hotkeys
Connector(s)	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	4 - VGA (15 pin, High Density D-Sub) Female 8 - 3.5 mm Mini-Jack (3 Position) Female
Software	OS Compatibility	OS independent; No software or drivers required
Power	Power Source	USB-Powered
Physical Characteristics	Cable Length	4 ft [1.2 m]
	Color	Black
	Enclosure Type	Plastic
	Product Depth	2.4 in [61 mm]
	Product Height	1 in [25 mm]
	Product Weight	6.7 oz [189 g]
	Product Width	3.7 in [95 mm]

Packaging Information	Shipping (Package) Weight	3.1 lb [1.4 kg]
What's in the Box	Included in Package	1 - 4 Port KVM Switch 4 - 4ft. Audio Cable (3.5mm speaker/mic) 4 - 4ft. VGA USB KVM Cable 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.