





## LLTHC 30 SU TO P5

Slim-line carriage, short length, standard height



Size:	30
W1 [mm]:	60
N [mm]:	16
H [mm]:	42
H2 [mm]:	11.3
H3 [mm]:	9
L1 [mm]:	78
L2 [mm]:	45
L3 [mm]:	
L4 [mm]:	14.6
W3 [mm]:	40

Date: 19/02/2019

© SKF is a registered trademark of the SKF Group.  
© SKF 2010

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

## LLTHC 30 SU T0 P5

Slim-line carriage, short length, standard height

H4 [mm]:	8.5
H5 [mm]:	8
D3 [mm]:	
S2:	M8
W [mm]:	28
H1 [mm]:	26
H6 [mm]:	13.8
F [mm]:	80
D1 [mm]:	9
D2 [mm]:	14
Emin [mm]:	12
E <sub>max</sub> [mm]:	70
L <sub>max</sub> [mm]:	3944
Weight [kg]:	0.48
Weight [kg/m]:	4.8
C [N]:	19200
C <sub>0</sub> [N]:	26600
M <sub>x</sub> [Nm]:	242
M <sub>x0</sub> [Nm]:	335
M <sub>y/z</sub> [Nm]:	120
M <sub>y0/z0</sub> [Nm]:	166
Preload class:	Zero preload T0
Precision class:	Standard P5

Date: 19/02/2019

© SKF is a registered trademark of the SKF Group.  
© SKF 2010

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.