

Datasheet

Silicone Heater Jacket 800 x 1950mm (1800mm Heated length)

RS Stock Number 179-9549



Description

Manufactured from silicone coated glass fibre cloth with a stitched glass filament thermal insulation layer. Fixing is via quick release buckles on high temperature webbing straps.

The internal heating element comprises high performance resistance wire spiral wound on to a glass core with silicone extruded insulation.

Temperature control is by an inbuilt thermostat. The actual maximum running temperature achievable will depend on the product being heated

Technical Specification

Electrical Rating: 230V 1800W

Suits Drum Diameter: 575mm to 595mm

Features and Benefits

- Silicone Rubber/Fibre Glass Jacket
- IP40 Protection
- Double Insulated Construction
- Moisture and Chemical Resistant
- Simple Strap & Buckle Fixing
- 4m Power Cable

High Temperature Heating Jacket Products		
Jacket Size	Thermostat	Stock No.
800 x 1950mm (1800mm Heated)	20-220°C Dial	179-9548
800 x 1950mm (1800mm Heated)	0-200°C Digital	179-9549

Applications

The ideal solution to heating products contained in standard 200l steel drums