

Technical Datasheet

3M™ Headlights



Product Description

3M™ Headlights are the perfect solution for anyone working in dimly lit conditions. The high-output LED lights clip to each temple arm allowing the user to quickly and easily light their work area. Two interchangeable clip sizes are available, allowing the user to select the one most compatible with their eyewear.

Product Range

26-4000-00M 3M™ Headlights

Key Features

- High-output LED
- Compatible with the majority of spectacle arms
- Pivoting attachment allows for directional lighting
- Two clip sizes available

Applications

These products can be used in a wide range of applications including:

- Maintenance and repair
- General assembly
- Construction
- Mechanical work

Approval

This product has been shown to meet requirements for Electromagnetic Compatibility (EMC) in accordance with Directive 2004/108/EEC as amended by 92/31/EEC and 93/68/EEC.

Technical specifications

Luminous flux	≥5 lumens
Battery life	≥6 hours (at ≥ 5 lumens)
Battery	LR44 1.5V Alkaline Button Cell (3 batteries per headlight)
Size	45.5*22*25mm
Weight	10 grams

Use Limitation

- Never modify or alter this product
- This product is not intrinsically safe and should not be used in explosive atmospheres.



Occupational Health & Safety Division EMEA Region

3M Centre,
Cain Road, Bracknell
Berkshire RG12 8HT
United Kingdom
Tel: +44 (0) 1344 858000
www.3M.eu/Safety

Company name

Address line 1
Address line 2
Region / City
Country
Tel Number
Web URL

15795

3M is a trademark of 3M company.
Please recycle. Printed in UK.
© 3M 2012. All rights reserved 3M.