



ENGLISH

Datasheet

RS Pro Non-Fused Terminal Block, 12 Way/Pole, Screw Down Terminals, 6 mm² Through Hole, Nylon, 400 V

RS Stock No: **492-8716**



Product Details

RS Pro non-fused terminal block in natural colour, has 12-way terminal blocks. This through hole block with 6-mm² wire, features screw down termination. The terminal block made of nylon, has 400 V voltage rating.

Features and Benefits

- Brass contact material
- Nickel contact plating
- Current rating of 41 A
- 12 mm pitch

**Specifications:**

Contact Material	Brass
Contact Plating	Nickel
Current Rating	41 A
Material	Nylon
Maximum Operating Temperature	+125°C
Mounting Type	Through Hole
Number of Ways	12
Pitch	12 mm
Termination Method	Screw Down
Voltage Rating	400 V
Wire Size	6 mm ²
Colour	Natural
Screw Size	M3.5 x 6
Standards Met	RoHS, CE, UL 94V-2, IEC 695-2-1, 2