


251A.2,5 | 251A - PRECISION SLEEVED DRIFT PUNCHES




Description :

- The centre slides within a guide to prevent distortion, even in smaller sizes.
- Shank hardened to 52 to 57 HRc.
- Zinc-plated body, burnished body.



Informations :

	251A.2,5
A [mm]	2,4
d [mm]	4,5
L [mm]	93
L1 [mm]	22
[g]	18