

## R.208-25 | R-J-S.208 - CLICK WRENCHES WITH FIXED RATCHET




### Norm :

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

### Description :

- Accuracy:  $\pm 4\%$ .
- Reliability of mechanism 25 000 cycles.
- Ratchet with 72 teeth ( $5^\circ$  increment) for use with sockets.
- One-way wrenches.
- Sensitive sound click when reaching torque.
- Automatic reset.
- Supplied with ISO 6789 calibration certificate.
- Supplied in plastic protection tube.

### Informations :

	R.208-25
L [mm]	300
Capacity [N.m]	5 - 25
Square ["]	1/4
Graduation [N.m]	0,1
[kg]	0.5