

54V XR FLEXVOLT TRIMMER & BRUSHCUTTER
DCM571X1

Line Diameter	7.5m x 2.0mm
Cutting Speed	0-5100rpm/0-5600rpm
Cutting Width/Swathe	38cm
Brush Cutter	Yes
Sound Power Level	94dB(A)



DCM571N - BARE UNIT DT20652-QZ LINE 2.5M X 68.6M DT20656-QZ CAP, SPOOL & LINE
DT20653-QZ BRUSH CUTTER TRI BLADE DT20654-QZ BRUSH CUTTER STRAIGHT BLADE
DT20655-QZ BRUSH CUTTER 4T BLADE

54V XR FLEXVOLT BLOWER
DCM572X1

Blow Speed	0-207km/h
Blow Area Volume	0-423cfm
Variable Speed	Yes
Lock On Switch	Yes
Sound Power Level	99.5dB(A)


DCM572N - BARE UNIT
54V XR FLEXVOLT 40CM CHAINSAW
DCM575X1

Bar and Chain Length	40cm
Chain Speed	15m/s
Chain Brake	< 1sec
Variable Speed	Yes
Chain Tensioning	Tool Free
Sound Power Level	100.5dB(A)



Tree Surgeon's License is NOT required to operate this machine

DCM575N - BARE UNIT DT20660-QZ BAR DT20662-QZ OIL DT20663-QZ 40CM REPLACEMENT CHAIN
DT20661-QZ 46CM BAR DT20664-QZ 46CM REPLACEMENT CHAIN

54V XR FLEXVOLT COMPRESSOR
DCC1054T2

Tank Size	10L
Power	0.3kW/0.4HP
Pump Type	Oil-free
Max. Pressure	9.3Bar
Free Air Delivery	31 l/min @ 7Bar
Noise LPa 1sd	79dB(A)
Weight	11kg
18GA Brad Nails per Charge	1220 on 1x 6.0Ah
Regulator Type	OneTurn™


DCC1054N - BARE UNIT
54V XR FLEXVOLT DUAL HANDLE PADDLE MIXER
DCD240X2

No Load Speed	225/350/475/600/725rpm
Hand/Arm Vibration	<2.5m/s²
Power Output	2000W
Max. Capacity	160mm
Ramp Up/Down Speed	2.5 secs
Spindle thread	m14
Battery Cover	Yes



Includes Centre Pull Down Swirl Paddle (550 x 200mm)

DCD240N - BARE UNIT
54V XR FLEXVOLT M-CLASS DUST EXTRACTOR
DCV586MT2

Extraction Classification	M-Class
Tank Capacity	15L
Wet/Dry	Yes
Hose length	2.5m
Hose Connection	AIRLOCK
Hose Diameter	32mm
Blower	No


DCV586N - BARE UNIT