

Datasheet

RS Pro HSS 65 mm 90° Countersink Drill Bit, 15 mm Head Diameter

RS Stock No: **215-445**



Product Details

RS Pro countersink drill bit has HSS construction for added durability. This 65 mm long drill bit with 90° countersink angle has a head diameter of 15 mm. The cutter with 90° angle is designed for chatter-free deburring and chamfering on a variety of materials at production speeds.

Features and Benefits

- Shank diameter of 10 mm
- 37.5 mm long shank
- 65 mm overall length
- Made from HSS



Specifications:

Countersink Angle	90°
Head Diameter	15 mm
Material	HSS
Overall Length	65 mm
Shank Diameter	10 mm
Shank Length	37.5 mm