


Receptacle strips TL, pre-wired for installation

with cable grip. Enclosure and insert made of **Amaplast**.

Receptacle strips can also be supplied with SCHUKO® type receptacles 16A, 230V, 2P+E or French/Belgian, British, Danish and Swiss standards:




Protection type **IP 44**



a	401
b	97
c	63
d	364
e	56
f	5,5
g.	4
Pg	16
Pg*	16
Dim. in mm	

Hanging clip enclosed with each receptacle strip




Cable entry:



1 x Pg 16 plugged at the top

1 x Pg 16 with gland at the bottom


This drawing is applicable for products on pages 128 and 129



3 CEEform receptacles
16A, 400V, 5P
with terminal
Part No. 96705




3 CEEform receptacles
16A, 230V, 3P
with terminal
Part No. 96489




3 CEEform receptacles
16A, 100-300 Hz, 4P
with terminal
Part No. 95937




3 CEEform receptacles
16A, 110V, 3P
with terminal
Part No. 96227



2 CEEform receptacles
16A, 400V, 5P
1 SCHUKO® type
receptacle
16A, 230V, 2P+E
with terminal
Part No. 96703



1 CEEform receptacle
16A, 400V, 5P
1 CEEform receptacle
16A, 230V, 3P
1 SCHUKO® type receptacle
16A, 230V, 2P+E
with terminal
Part No. 96702







1 CEEform receptacle
16A, 400V, 5P
2 SCHUKO® type receptacles
16A, 230V, 2P+E
with terminal
Part No. 96438



Receptacle strips TL, pre-wired for installation


with cable grip. Enclosure and insert made of Amaplast.

Receptacle strips can also be supplied with SCHUKO® type receptacles 16A, 230V, 2P+E or French/Belgian, British, Danish and Swiss standards:




Protection type Δ IP 44

When the receptacle strip shown on page 128 is mounted horizontally the receptacles mounted on it can be turned 90° without dislodging the connection leads.



Other variations on request!


6



3 CEEform receptacles
16A, 400V, 5P
Fuse/protection:
1 RCD \boxtimes 25A, $I_{\Delta N} = 0.03A$
Part No. 95472




1 CEEform receptacle
16A, 400V, 5P
1 CEEform receptacle
16A, 230V, 3P
1 SCHUKO® type receptacle
16A, 230V, 2P+E
Fuse/protection:
1 RCD \boxtimes 25A, $I_{\Delta N} = 0.03A$
Part No. 95471




3 SCHUKO® type receptacles
16A, 230V, 2P+E
with terminal
Part No. 95996



1 SCHUKO® type receptacles
6A, 230V, 2P+E
with terminal
Part No. 88677



3 SCHUKO® type receptacles
16A, 230V, 2P+E
with terminal
Part No. 96700



a	308
b	75
c	70
d	273
e	55,5
f	4,5
g	4
k	57
Pg	16
Pg*	16
Dim. in mm	



4 SCHUKO® type receptacles
16A, 230V, 2P+E
with terminal
Part No. 88678

