






Socket Terminals



Wire Wrap Terminals



Board to Board Terminals

<p>Terminal 037 dimensions: ϕ 0.64 / .025, 4.22 / .166, ϕ 1.83 / .072, 3.93 / .154, ϕ 1.35 / .053, 3.96 / .156, ϕ 0.46 / .018.</p>	<p>Terminal 056 dimensions: ϕ 0.65 / .025, 4.68 / .184, ϕ 1.52 / .060, 14.82 / .583, ϕ 1.83 / .072, 1.35 / .053, 3.40 / .134, ϕ 0.46 / .018.</p>	<p>Terminal 057 dimensions: ϕ 0.65 / .025, 4.10 / .161, ϕ 1.83 / .072, 3.90 / .153, ϕ 1.35 / .053, 7.19 / .283, ϕ 0.50 / .019.</p>	<p>Terminal 058 dimensions: ϕ 0.46 / .018, 3.56 / .140, ϕ 1.52 / .060, 8.89 / .350, ϕ 1.83 / .072, 1.35 / .053, 3.40 / .134, ϕ 0.46 / .018.</p>	<p>Terminal 059 dimensions: ϕ 0.46 / .018, 3.56 / .140, ϕ 1.52 / .060, 11.61 / .457, ϕ 1.83 / .053, 1.35 / .072, 3.40 / .134, ϕ 0.46 / .018.</p>	
<p>Terminal 077 dimensions: ϕ 0.46 / .018, 4.22 / .166, ϕ 1.83 / .072, 3.68 / .144, ϕ 1.35 / .053, 3.96 / .156, ϕ 0.46 / .018.</p>	<p>Terminal 078 dimensions: ϕ 0.64 / .025, 12.95 / .509, ϕ 1.83 / .072, 3.94 / .155, ϕ 1.35 / .053, 3.96 / .155, ϕ 0.46 / .018.</p>	<p>Terminal 220 dimensions: ϕ 0.46 / .018, 4.22 / .166, ϕ 1.83 / .072, 3.34 / .131, ϕ 1.35 / .053, 5.80 / .228, ϕ 0.64 / .025.</p>	<p>Terminal 372 dimensions: ϕ 0.51 / .020, 4.22 / .166, ϕ 1.60 / .062, 3.93 / .154, ϕ 1.35 / .053, 3.96 / .156, ϕ 0.46 / .018.</p>	<p>Terminal 377 dimensions: ϕ 0.46 / .018, 3.17 / .124, ϕ 1.78 / .070, 1.45 / .057, ϕ 1.32 / .052, 2.71 / .106, ϕ 0.46 / .018.</p>	
<p>Terminal 542 dimensions: ϕ 0.46 / .018, 2.95 / .116, ϕ 1.48 / .058, 19.05 / .750, ϕ 1.83 / .072, 1.35 / .053, 3.40 / .133, ϕ 0.46 / .018.</p>	<p>Terminal 544 dimensions: ϕ 0.46 / .018, 3.56 / .140, ϕ 1.18 / .046, 10.50 / .413, ϕ 1.83 / .072, 1.35 / .053, 3.40 / .133, ϕ 0.46 / .018.</p>	<p>Terminal 562 dimensions: ϕ 0.46 / .018, 3.56 / .140, ϕ 1.48 / .058, 14.82 / .583, ϕ 1.83 / .072, 1.35 / .053, 3.40 / .133, ϕ 0.46 / .018.</p>	<p>Terminal 583 dimensions: ϕ 0.46 / .018, 3.56 / .140, ϕ 1.20 / .047, 5.70 / .224, ϕ 1.83 / .053, 2.40 / .094, ϕ 1.35 / .072, ϕ 0.46 / .018.</p>	<p>Terminal 770 dimensions: ϕ 0.46 / .018, 3.60 / .141, ϕ 1.80 / .070, 3.50 / .138, ϕ 1.35 / .053, 2.90 / .114, ϕ 0.46 / .018.</p>	<p>for pitch 1,27mm/.050"</p> <p>Terminal 774 dimensions: ϕ 0.44 / .017, 2.40 / .094, ϕ 1.00 / .039, 6.05 / .238, ϕ 0.85 / .033, 2.85 / .112, ϕ 0.44 / .017.</p>

Header Terminals

<p>Terminal 036 dimensions: ϕ 0.96 / .038, 3.81 / .150, 3.99 / .157, 12.47 / .491, ϕ 1.60 / .063, 6.58 / .259, ϕ 2.00 / .079, 3.96 / .156, ϕ 1.35 / .053, ϕ 0.46 / .018.</p>	<p>Terminal 353 dimensions: ϕ 0.90 / .035, 2.55 / .100, 4.00 / .157, 3.45 / .135, ϕ 1.80 / .070, 3.15 / .124, ϕ 1.35 / .053, ϕ 0.50 / .019.</p>	<p>Terminal 038 (Wire Wrap) dimensions: ϕ 0.90 / .035, 2.50 / .098, 3.50 / .137, 2.90 / .114, 12.62 / .496, ϕ 1.83 / .072, ϕ 1.35 / .053, ϕ 0.64 / .025.</p>			
--	---	--	--	--	--