

# Selection table metal

		Contacts		Back shell with...																													
		Pin	Socket	Strain relief <sup>1</sup>						Shrink hose <sup>2</sup>			PG-thread <sup>2</sup>						M-thread <sup>2</sup>						Cable screw attachment <sup>2</sup>								
				TT93XXP-XX	TT93XXS-XX	TM118SR-33	TM118SR-45	TM178SR-45	TM178SR-70	TM238SR-70	TM238SR-112	TM118ES-26	TM178ES-40	TM238ES-55	TM118GA-PG9	TM118GA-PG11	TM178GA-PG11	TM178GA-PG13	TM238GA-PG16	TM238GA-PG21	TM238GA-PG29	TM118GA-M16	TM118GA-M20	TM178GA-M20	TM238GA-M20	TM238GA-M25	TM238GA-M32	TM238GA-M40	TM118UD-152	TM178UD-152	TM178UD-154	TM238UD-153	TM238UD-155
Connector	TM1110-P04	o		o	o				o			o	o						o	o							o						
	TM1110-S04		o	o	o				o			o	o						o	o							o						
	TM1710-P09	o				o	o							o	o							o							o	o			
	TM1710-P14	o				o	o							o	o							o							o	o			
	TM1710-S09		o			o	o							o	o							o							o	o			
	TM1710-S14		o			o	o							o	o							o							o	o			
	TM2310-P24	o						o	o								o	o	o				o	o	o	o					o	o	
	TM2310-P37	o						o	o								o	o	o				o	o	o	o					o	o	
	TM2310-S24		o					o	o								o	o	o				o	o	o	o					o	o	
	TM2310-S37		o					o	o								o	o	o				o	o	o	o					o	o	
Panel-mounted socket	TM1131-P04	o		o	o				o			o	o						o	o						o	o						
	TM1131-S04		o	o	o				o			o	o						o	o						o	o						
	TM1731-P09	o				o	o							o	o							o							o	o			
	TM1731-P14	o				o	o							o	o							o							o	o			
	TM1731-S09		o			o	o							o	o							o							o	o			
	TM1731-S14		o			o	o							o	o							o							o	o			
	TM2331-P24	o						o	o							o	o	o					o	o	o						o	o	
	TM2331-P37	o						o	o							o	o	o					o	o	o						o	o	
	TM2331-S24		o					o	o							o	o	o					o	o	o						o	o	
	TM2331-S37		o					o	o							o	o	o					o	o	o						o	o	
Cable-mounted socket	TM1121-P04	o		o	o				o	o		o	o						o	o						o							
	TM1121-S04		o	o	o				o	o		o	o						o	o						o							
	TM1721-P09	o				o	o							o	o							o							o	o			
	TM1721-P14	o				o	o							o	o							o							o	o			
	TM1721-S09		o			o	o							o	o							o							o	o			
	TM1721-S14		o			o	o							o	o							o							o	o			
	TM2321-P24	o						o								o	o	o					o	o	o	o					o	o	
	TM2321-P37	o						o								o	o	o					o	o	o	o					o	o	
	TM2321-S24		o					o								o	o	o					o	o	o	o					o	o	
	TM2321-S37		o					o								o	o	o					o	o	o	o					o	o	

<sup>1</sup> Standard version with back shell seal, not used for sealing purposes

<sup>2</sup> Standard version with back shell seal

<sup>3</sup> Standard version with seal to device wall

<sup>4</sup> Standard version with insertion area seal

## Selection table metal

Back shell with... Shureseal adapter <sup>2</sup>							90° angled adapters <sup>3</sup>			Protective caps <sup>4</sup>						Flange			Seals <sup>5</sup>			Back shell			Insertion area			Contact support holder		
TM118F-0375	TM118F-0500	TM178F-0375	TM178F-0500	TM178F-0750	TM238F-0500	TM238F-0750	TM238F-1000	TM118-90	TM178-90	TM238-90	TT18-DCP	TT178DCP	TT238DCP	TT118DCR	TT178DCR	TT238DCR	TM118GSK	TM178GSK	TM238GSK	TM118ED	TM178ED	TM238ED	TT118SR	TT178SR	TT238SR	TM118RET	TM178RET	TM238RET		
○	○										○									○							○			
○	○										○									○							○			
		○	○	○								○									○							○		
		○	○	○								○									○							○		
		○	○	○								○									○							○		
		○	○	○								○									○							○		
					○	○	○						○									○							○	
					○	○	○						○									○							○	
					○	○	○						○									○							○	
					○	○	○						○									○							○	
					○	○	○						○									○							○	
○	○							○						○						○							○			
○	○							○						○						○							○			
		○	○	○					○					○							○							○		
		○	○	○					○					○							○							○		
		○	○	○					○					○							○							○		
					○	○	○							○								○							○	
					○	○	○							○								○							○	
					○	○	○							○								○							○	
					○	○	○							○								○							○	

<sup>5</sup>Also as a spare part

○ Accessories  
● Series