

Selection table plastic

		Contacts		Back shell with...																							
		Pin	Socket	Strain relief						Shrink hose ¹			PG-thread ²						M-thread ²								
				TT93XXP-XX	TT93XXS-XX	TT118SR-33	TT118SR-45	TT178SR-45	TT178SR-70	TT238SR-70	TT238SR-112	TT118ES-26	TT178ES-40	TT238ES-55	TT118GA-PG9	TT118GA-PG11	TT178GA-PG11	TT178GA-PG13	TT238GA-PG16	TT238GA-PG21	TT238GA-PG29	TT118GA-M16	TT118GA-M20	TT178GA-M20	TT238GA-M20	TT238GA-M25	TT238GA-M32
Connector	TT1110-P04	o		o	o					o			o	o						o	o						
	TT1110-S04		o	o	o					o			o	o						o	o						
	TT1710-P09	o				o	o								o	o						o					
	TT1710-P14	o				o	o								o	o						o					
	TT1710-S09		o			o	o								o	o						o					
	TT1710-S14		o			o	o								o	o						o					
	TT2310-P24	o						o	o			o					o	o	o				o	o	o	o	o
	TT2310-P37	o						o	o			o					o	o	o				o	o	o	o	o
	TT2310-S24		o					o	o			o					o	o	o				o	o	o	o	o
	TT2310-S37		o					o	o			o					o	o	o				o	o	o	o	o
Panel-mounted socket	TT1130-P04	o		o	o					o			o	o						o	o						
	TT1130-S04		o	o	o					o			o	o						o	o						
	TT1730-P09	o				o	o								o	o						o					
	TT1730-P14	o				o	o								o	o						o					
	TT1730-S09		o			o	o								o	o						o					
	TT1730-S14		o			o	o								o	o						o					
	TT2330-P24	o						o	o			o					o	o	o				o	o	o	o	o
	TT2330-P37	o						o	o			o					o	o	o				o	o	o	o	o
	TT2330-S24		o					o	o			o					o	o	o				o	o	o	o	o
	TT2330-S37		o					o	o			o					o	o	o				o	o	o	o	o
Cable-mounted socket	TT1120-P04	o		o	o					o			o	o						o	o						
	TT1120-S04		o	o	o					o			o	o						o	o						
	TT1720-P09	o				o	o								o	o						o					
	TT1720-P14	o				o	o								o	o						o					
	TT1720-S09		o			o	o								o	o						o					
	TT1720-S14		o			o	o								o	o						o					
	TT2320-P24	o						o	o			o					o	o	o				o	o	o	o	o
	TT2320-P37	o						o	o			o					o	o	o				o	o	o	o	o
	TT2320-S24		o					o	o			o					o	o	o				o	o	o	o	o
	TT2320-S37		o					o	o			o					o	o	o				o	o	o	o	o

¹ Standard version with back shell seal

² Optional with back shell seal

³ Standard version with seal to device wall

⁴ Standard version with insertion area seal

Selection table plastic

Back shell with ...					90° angled adapters ³			Protective caps ⁴						Flange			Seals					
Cable screw attachment ²																	Back shell		Insertion area			
TT118UD-152	TT178UD-152	TT178UD-154	TT238UD-153	TT238UD-155	TT118-90	TT178-90	TT238-90	TT118-DCP	TT178DCP	TT238DCP	TT118DCR	TT178DCR	TT238DCR	TT118GSK	TT178GSK	TT238GSK	TT118ED	TT178ED	TT238ED	TT118SR	TT178SR	TT238SR
○								○									○					
○								○									○					
	○	○							○									○				
	○	○							○									○				
	○	○							○									○				
	○	○							○									○				
			○	○						○									○			
			○	○						○									○			
			○	○						○									○			
			○	○						○									○			
			○	○						○									○			
			○	○						○									○			
			○	○						○									○			
○											○									○		
○											○									○		
	○	○										○						○			○	
	○	○										○						○			○	
	○	○										○						○			○	
	○	○										○						○			○	
			○	○									○						○			○
			○	○									○						○			○
			○	○									○						○			○
			○	○									○						○			○

⁵ Also as a spare part

○ Accessories